

Anesthesia Workstation

Located in the corner away from the OR entry with ample space to minimize interruptions

Anesthesia Storage

Located within anesthesia work area and across the monitor to provide quick access for the anesthesia team with minimal obstruction.

Angled OR table position


OR table angled to accommodate sidedness of surgery and ample space for the scrub nurse's maneuver

Scrub Sink Window

Scrub sink strategically located and equipped with a window to provide view into the OR

Flexible room/suite chassis

Flexibility, adaptability and expandability to accommodate changing needs and future expansion



Parallel processing

Dedicating an induction room to process two patients simultaneously inside and outside of the OR can increase patient and parent satisfaction and patient throughput

Integrated Digital Information Displays

Wall mounted screens to maximize visual awareness

General Storage

Located near CN's workstation to accommodate quick access to supplies and material by the CN

Provision of sufficient circulation area

Optimize movement and flow in the operating room

Circulating Nurse Workstation

Mobile CN workstation provided flexibility with rotation and move of the workstation as needed.

Integrated Digital Information Displays

Conveniently provide information needed on vitals and patient information with minimal body movement and adjustment